

4



3

2

1

used for:

D-SUB



No. of pos.	A	B	C	D	E	F	Part NO.
9	34.0	25.0	25.0	27.75	14.5	8.5	165X11059X
15	42.3	33.3	37.0	39.75	14.5	10.0	165X11069X
25	56.0	47.0	37.0	39.75	14.5	10.5	165X11079X
37	72.5	63.5	37.0	39.75	14.5	10.5	165X11089X


Directive 2002/95/EC
"RoHS"
Compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.

OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance



scale:

1:1

material:

ABS UL 94 V-0
metallized

title:

PLASTIC HOOD

9-37pos.

with straight cable exit and screw lock

dwg no:

AutoCAD 2000

DIN-A

16K1A358A

4

sh: 1/1

part no:

SEE TABLE

CONEC[®]

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[165X11059X](#)