

4




3

2

1

used for:

D-SUB



SLIDE LOCK

POS.	A	B	C	D max. cable ϕ	E	F	Part No: Bulk package
9	32.0	25.0	36.7	6.3	15.5	16.5	165X11279X
15	40.0	33.3	38.2	8.0	15.5	16.5	165X11289X
25	54.2	47.0	42.2	10.5	15.5	16.5	165X11299X (165X11299X-S)
37	70.6	63.5	47.2	11.5	15.5	16.5	165X11309X
50	68.2	61.1	47.2	13.7	19.6	20.6	165X16549X

MATERIAL:

HOOD: ABS UL 94 V-0; BLACK


SLIDE LOCK: STEEL; NICKEL PLATED

SPRING: STEEL; TIN PLATED

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
6x b	Ä 2620	05.12.2006	ES

tolerance



2000	date	name
drawn	03.07.	A. Mickenbecker
appd.	03.07.	E. Mickenbecker
norm		
d-old		

scale:

1:1

material:

SEE NOTES

title:

PLASTIC HOOD

9-50pos. with top and side cable exit
with slide lock

dwg no:

AutoCAD 2000

DIN-A

16K1A024A

4

sh: 1/1

product no:

SEE TABLE

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[165X11309X](#)