





9pos.



15pos. - 50pos.



spring

slide lock

screws

					(b)	(c)		
No. of pos.	A	B	C	ØD	Blind Plug included	Part-No. Bulk package	Part-No. Single package	
9 (b)	32.0	25.0	14.8	12.1	1	165X11659X	165X11659XE	
15	39.3	33.3	14.8	12.1	2	165X11669X	165X11669XE	
25	53.2	47.0	14.8	12.1	2	165X11679X	165X11679XE	
37	69.5	63.5	14.8	12.1	2	165X11689X	165X11689XE	
50	67.0	61.1	17.8	14.6	2	165X11699X	165X11699XE	

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL


THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.

DO NOT ALTER CAD DRAWING BY HAND

1 x c	Ä 3720	18.08.10	Lehm.
4 x b	Ä 2240	24.05.05	HS
a	Origin		
rev.	description	date	name



tolerance



scale:	1:1
material:	Hood: die-cast zinc

	title:	METAL HOOD
r		EMI/RFI SHIELDING 9 - 50 pos.
		with slide lock

dwg no:	AutoCAD 2000
---------	--------------

16K1A688

part no:	SEE TABLE
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[165X11659X](#) [165X11669X](#) [165X11679X](#) [165X11699X](#) [165X11689X](#)