

4



3

2

1

used for:

D-SUB



No. of pos.	A	B	C	D	ϕE	Part No:
9	33.0	25.0	45.0	17.0	7.5	165X13019X
15	41.0	33.3	45.0	17.0	8.5	165X13029X
25	55.0	47.0	47.0	17.0	10.5	165X13039X
37	71.3	63.5	51.0	17.0	11.0	165X13049X
50	69.0	61.1	50.0	20.0	12.5	165X13059X

Directive 2002/95/EC
"RoHS"
Compliant

NOTES:

- HOOD: ABS UL 94 V-0
- SCREWS: BRASS

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		
rev.	description	date	name	2001	date	
				drawn	02.10.	Parei
				appd.	02.10.	Mickenbecker
				norm		
				d-old		

scale:	1:1	
material:	SEE NOTES	
title:	PLASTIC HOOD with straight and side cable entry with short screws, 9 - 50 pos.	
dwg no:	AutoCAD 2000	DIN-A
	16K1A320A	4
		sh: 1/1
part no:	SEE TABLE	

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[165X13049X](#)