

4


3

2

1

used for:

D-SUB



No. of pos.	A	B	C	D	E	F	Part No:
9	34.0	25.0	25.0	27.75	14.5	8.5	165X14209X
15	42.3	33.3	37.0	39.75	14.5	10.0	165X14219X
25	56.0	47.0	37.0	39.75	14.5	10.5	165X14229X
37	72.5	63.5	37.0	39.75	14.5	10.5	165X14239X
50	70.0	61.1	50.0	50.00	21.0	10.5	165X14249X

NOTES:

- HOOD MATERIAL: POLYAMID + GF / GREY
- SCREWLOCK: MATERIAL: BRASS NICKEL-PLATING

Directive 2002/95/EC
RoHS
Compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance			
				2002	date	name	
				drawn	04.03.	Schmidt	
				appd.	04.03.	Mickenbecker	
				norm			
				d-old	KAT11Y5A		
							
rev.	description	date	name				

material:		SEE NOTES	
title:		PLASTIC HOOD with straight cable exit and screw lock, 9 - 50 pos.	
dwg no:		AutoCAD 2000	DIN-A
part no:		16K1A671	4
		SEE TABLE	

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[165X14209X](#)