

6

5

4

3



2

1

used for: D-SUB

ⓑ 9pos.

ⓑ 15-50pos.



ⓑ ⓐ

No. of pos.	A	B	C	D	E	ØF	Part-N0. Single package	Part-N0. Bulk package
9	32.9	25.0	39.5	41.8	16.3	11.0	165X14509XE	165X14509X
15	41.2	33.3	45.5	47.8	16.3	11.0	165X14519XE	165X14519X
25	54.9	47.0	52.5	54.8	16.3	12.0	165X14529XE	165X14529X
37	71.4	63.5	55.0	57.8	18.7	15.0	165X14539XE	165X14539X
50	69.0	61.1	55.0	57.8	19.5	14.0	165X14549XE	165X14549X

ⓑ HOOD ASSEMBLY CONSISTS OF:

- 1 x HOOD + COVER: PBT UL 94 V-0; BLACK
- 1 x PRESS INSERT: PBT UL 94 V-0; BLACK
- 2 x JACKSCREWS: BRASS; NICKEL PLATED
- 2 x SCREW FOR STRAIN RELIEF: STEEL; NICKEL PLATED
- 2 x COVER SCREWS: STEEL; NICKEL PLATED
- 1 x STRAIN RELIEF: STEEL; NICKEL PLATED

TECHNICAL DATA:

- TEMPERATURE RANGE: -40°C to +125°C ⓐ

ⓐ

Directive 2002/95/EC RoHS compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

3 x c	Ä5307	25.08.2014	E.Mick.	d-old
4 x b	Ä 2544	03.08.2006	Lehmen	
a	Origin			
rev.	description	date	name	

tolerance		dim. in mm
2001	date	name
drawn	23.11.	Parei
appd.	23.11.	Resonnek
norm		

scale:	1:1
material:	SEE DRAWING
title:	
PLASTIC HOOD 9-50pos. with straight cable exit	
dwg no:	AutoCAD 2006 DIN-A
16K1A380A	
part no:	SEE TABLE
sh: 1/1	

6

5

4

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[165X14519X](#)