

4



3

2

1

used for:

D-SUB



HOOD ASSEMBLY CONSISTS OF:

- 1 x HOOD + COVER: PBT UL 94 V-0; BLACK
- 1 x PRESS INSERT: PBT UL 94 V-0; BLACK
- 2 x JACKSCREWS: BRASS; NICKEL PLATED
- 2 x SCREW FOR STRAIN RELIEF: STEEL; ZINC PLATED
- 1 x COVER SCREWS: STEEL; NICKEL PLATED
- 1 x STRAIN RELIEF: STEEL; NICKEL PLATED

Pos.	ØF cable diameter	
	WITH PRESS INSERT	WITHOUT PRESS INSERT
9	4.0 - 6.3	6.4 - 8.6
15	4.0 - 6.3	6.4 - 8.6
25	6.5 - 8.5	8.6 - 12.0
37	8.5 - 10.9	11.0 - 14.0
50	8.5 - 10.9	11.0 - 14.0

TECHNICAL DATA:

- TEMPERATURE RANGE: -40°C to +125°C (b)

Directive 2002/95/EC RoHS compliant

(b) (b)

Pos.	A	B	C	D	E	Part No. Bulk package	Part Nr. Single package
9	32.9	25.0	39.5	41.9	16.4	165X14559X	165X14559XE
15	41.2	33.3	45.5	47.9	16.4	165X14569X	165X14569XE
25	54.9	47.0	52.5	54.9	16.4	165X14579X	165X14579XE
37	71.4	63.5	55.0	57.9	18.8	165X14589X	165X14589XE
50	69.0	61.1	55.0	57.9	19.6	165X14599X	165X14599XE

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance			
				2010	date	name	
				drawn	17.12.	Henneboel	
				appd.	17.12.	Fischer	
				norm			
				d-old			
3 x b	Ä5350	17.09.2014	E.Mick.				
a	Origin						
rev.	description	date	name				

scale:	1:1		
material:	SEE TECHNICAL DATA		
title:	PLASTIC HOOD WITH SIDE CABLE EXIT 9 to 50pos.		
dwg no:	AutoCAD	DIN-A	
	16K1A2754	4	
		sh: 1/1	
product no:	SEE TABLE		

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[165X14559X](#)