

6



5

4





3

2

1



Recommended Panel Cutout (b)

**Notes:**

1. Electrical Specifications:

- Meets EIA/TIA-568-B.2 Cat.5e Specification
- Contact Resistance: 20mOhm max.
- Insulation Resistance: 500MOhm min. @ 100 VDC
- Current Rating: 1.2A max. at 25° C
- Working Voltage: 100 VDC
- DWV: 1000 VDC/60s Contact to Contact, 1500 VDC/60s Contact to Metal Shell
- Operating Temperature: -40° C to +85° C

2. Material and Finish:

- Receptacle Housing: Metallized ABS (Nickel Plated); UL94 V-0
- Panel Nut: Brass, Finish: Nickel Plated
- Panel Gasket: Silicon, Color: White
- Cat.5e RJ45 PCB Jack Metal Shell: Copper Alloy, Nickel Plated
- Cat.5e RJ45 PCB Jack Plastic Housing: Glass filled PBT UL94 V-0, Color: Black
- Cat.5e RJ45 PCB Jack Contacts: Phosphor Bronze, Finish: 50u" Gold min. over Nickel

3. Connector can be front or rear mounted to a maximum panel thickness of 3.2mm.

4. IP67 rated when covered or fully mated with the appropriate mating connector

5. RoHS compliant

Directive 2002/95/EC RoHS Compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3				Scale: 1.5:1		Dim. in mm	
	Name		Title	Approval Date		Autodesk Inventor		Material: See Notes			
								Title: Receptacle Assembly Kit			
								Metallized Plastic Receptacle Housing			
								with Shielded Cat. 5e RJ45 PCB Jack			
								Drawing No.: 17K1A192			
								Part No.: 17-10018			
								DIN A3			
								Sheet 1/1			

Customer:				Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3				Scale: 1.5:1		Dim. in mm	
Name		Title	Approval Date		Autodesk Inventor		Material: See Notes				
							Title: Receptacle Assembly Kit				
							Metallized Plastic Receptacle Housing				
							with Shielded Cat. 5e RJ45 PCB Jack				
							Drawing No.: 17K1A192				
							Part No.: 17-10018				
							DIN A3				
							Sheet 1/1				

Customer:				Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3				Scale: 1.5:1		Dim. in mm	
Name		Title	Approval Date		Autodesk Inventor		Material: See Notes				
							Title: Receptacle Assembly Kit				
							Metallized Plastic Receptacle Housing				
							with Shielded Cat. 5e RJ45 PCB Jack				
							Drawing No.: 17K1A192				
							Part No.: 17-10018				
							DIN A3				
							Sheet 1/1				

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[17-10017](#) [17-10018](#)