




Notes:

- © 1. Material and Finish:
- Cover Coupling Ring: Polyester (Black) or metallized ABS, (Nickel Plated), or PBT (White, RAL9016), UL94 V-0
 - Ball Chain: Copper Alloy, Nickel Plated
 - Screw: Stainless steel, Nickel Plated
 - Cover Gasket: Silicon, Color: Transparent
2. Operating Temperature: -40°C to +85°C

Directive 2002/95/EC RoHS Compliant

Version	Part Number
Black Plastic Version with metal ball chain	17-101710
Metallized Plastic Version with metal ball chain	17-101720
White plastic version (Color #: RAL9016) with metal ball chain	17-103850

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. CONECSHIP AND COPYRIGHT OF CONEC CORPORATION	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3°			Scale:	Dim. in mm
	Name		Title	Approval Date		Material: See Notes		
				2009	Date	Name	Title: Protective Cover Assembly Kit Plastic or Metallized Plastic Version with metal ball chain	
				Draw.	Sept. 14	Vincent Ke		
				Appd.	Sept. 14	J. Chaudry		
				Norm				
	d	1 x d	Aug/08/2013	Vincent Ke	Norm			
	c	2 x c	Jul/09/2013	Vincent Ke	D-old			
b	1 x b	Mar/30/2010	Vincent ke		Drawing No.: 17K1A136	DIN A3		
a	original							
Rev.	Changes	Date	Name				Part No.: SEE PART NUMBER TABLE	Sheet 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[17-101710](#) [17-101720](#)