




NOTES:

1. Electrical Specifications:

- Meets USB 2.0 specifications
- Low level Contact Resistance: 30 mOhm max.
- Insulation Resistance 1000 MOhm min.
- Current Rating: 1.5 A max. @ 25°C
- DWV: 500 VAC/60s at sea level
- Operating Temperature: -40°C to +80°C

2. Material and Finish:

- USB Insulato: PBT, UL 94V-0, Color: White
- USB Overmold: PVC, UL 94V-0, Color: Black
- Metal Shell: Copper Alloy, Nickel plated
- Contact Material: Copper Alloy Contact Finish: 30 u" min. Au over 40 u" min. Nickel

3. Shielded USB Cable Configuration

- AWM 2725 AWG28/1p + AWG24/2c, OD: 4.5 mm, Color: black

Directive 2002/95/EC RoHS Compliant

ⓑ ⓐ
ⓓ ⓔ
ⓕ ⓖ

Cable Length L	Part Number
1 m	17-201021
2m	17-201031
3 m	17-201041
4m	17-201051
4.5 m	17-201061
5 m	17-200861

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. CONEC CORPORATION OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION. DO NOT ALTER CAD DRAWING BY HAND	Customer:				Tolerance Unless otherwise specified 0 PLC ±0.30 1 PLC ±0.20 2 PLC ±0.10 3 PLC ±0.05 ANGLES ±1°				Scale: NTS		Dim. in m	
	Name		Title		Approval Date		Autodesk Inventor		Material: See Notes			
									Title:			
	f	1 x f	Mar/19/2013	Vincent Ke	Draw.	Sept. 23	Vincent Ke		USB Patch Cord			
	e	1 x e	Jun/11/2012	Vincent ke	Appd.	Sept. 23	J. chaudry		Standard to Standard Version			
	d	1 x d	Sep/13/2011	Vincent ke	Norm				Type A Plug to Type A Plug			
	c	1 x c	Mar/08/2011	Vincent ke	D-old							
	b	1 x b	Jan/19/2009	Vincent ke					Drawing No.: 17K1A101			
	a	original							Part No.: SEE P/N ABOVE			
	Rev.	Changes	Date	Name								



DIN A3 Sheet 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[17-201031](#) [17-201041](#) [17-201061](#)