






POS.	A -0.76	B $+0.25$	C	D -0.3	Part NO.
9	31.19	16.79	25.00 $+0.12$ -0.13	6.12	241A10050X
15	39.52	25.12	33.30 $+0.15$ -0.1	6.12	241A10060X
25	53.42	38.84	47.04 ± 0.13	5.99	241A10070X
37	69.70	55.30	63.50 ± 0.13	5.99	241A10080X

used for: D-SUB FILTER



NOTES:

- METALSHELLS: STEEL; min. 320µ" TIN
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: 8µ" HARD GOLD OVER min. 50µ" NICKEL
- P.C.B. HOLE DRILLINGS ON SHEET 2
- CAPACITANCE: 1300pF $\pm 20\%$
- DIELECTRIC WITHSTANDING VOLTAGE: 424 VDC
- CONNECTOR IS PART MARKED: [PART-NO. CONEC ABC]
-  = CHECK DIMENSION

Directive 2002/95/EC
RoHS
Compliant





APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
3 x b	Ä 2419	02.01.2006	Lehmen

tolerance	dim. in mm
2005	date
drawn	18.10.
appd.	19.10.
norm	DIN 41652
d-old	
CONEC®	

scale:	2:1 (5:1)
material:	SEE NOTES
title:	
D-SUB FILTER MALE	
9-37pos. SOLDER PIN STRAIGHT	
dwg no:	AutoCAD 2004
24K1A710	
part no:	SEE TABLE



APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance	dim. in mm
2005	date
drawn	18.10.
appd.	19.10.
norm	DIN 41652
d-old	

scale:	2:1
material:	SEE SHEET 1
title:	P.C.B. HOLE DRILLINGS D-SUB FILTER MALE 9-37pos. SOLDER PIN
dwg no:	AutoCAD 2004
part no:	SEE SHEET 1



24K1A710

DIN-A
3
sh:2/2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[241A10080X](#) [241A10060X](#)