






used for: D-SUB HD FILTER ADAPTER

		PART NO.	
FILTER	CAPACITANCE	M3	4-40 UNC
TYPE 1	180pF±20%	243811720X	243811600X
TYPE 3	370pF±20%	243811760X	243811640X
TYPE 4	830pF±20%	243811800X	243811680X

**NOTES:**

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: § USE A FOR QUALITY CLASS 3 (8µin HARD GOLD OVER min. 50µin NICKEL)
§ USE B FOR QUALITY CLASS 2 (20µin HARD GOLD OVER min. 50µin NICKEL)
§ USE C FOR QUALITY CLASS 1 (30µin HARD GOLD OVER min. 50µin NICKEL)
4. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

Directive 2002/95 EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACON # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACON # APPROVAL
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACON # APPROVAL	APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACON # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
1 x b	Ä 2535	18.07.2006	Lehmen
a	Origin		

tolerance		dim. in mm	scale: 2:1 (5:1)
1997	date		
drawn	28.01.	Barcinski	D-SUB HD FILTER ADAPTER 15pos.
appd.	28.01.	Mickenbecker	
norm		DIN 41652	
d-old			

CONEC

scale:		2:1 (5:1)	
material:		SEE NOTES	
title:			
D-SUB HD FILTER ADAPTER			
15pos.			
dwg no:		AutoCAD 2006	DIN-A
24K11P7A			3
			sh: 1/1
part no:		SEE TABLE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[243A11680X](#)