





used for: D-SUB IDC CONNECTOR


POS.	A ^{+0.13 -0.12}	B ^{+0.25}	C ^{+0.12 -0.13}	D ^{+0.25}	E	F ^{+0.13}	G ^{+0.13}	H ^{+0.13}	J ^{+0.13}	K ^{+0.13}	L ^{+0.25}	M ^{+0.25}	Part NO.
9	24.99	30.80	16.92	16.10	5.90 ^{+0.15 -0.08}	20.5	22.2	25.00	11.4	13.0	19.15	16.10	301A10089X
15	33.32	39.10	25.25	24.00	5.90 ^{+0.15 -0.08}	28.8	30.5	33.30	11.4	13.0	27.15	24.00	301A10099X
25	47.04	53.09	38.97	38.14	5.90 ^{+0.09 -0.14}	42.5	44.3	47.04	11.4	13.0	41.45	38.14	301A10109X
37	63.50	69.40	55.43	54.60	5.90 ^{+0.09 -0.14}	59.1	60.7	63.50	11.4	13.0	57.65	54.60	301A10119X




STRAIN RELIEF



① RECOMMENDED PANEL CUT-OUT



REAR PANEL MOUNTING



FRONT PANEL MOUNTING



① ② ③ ④ ⑤ SPECIFICATION :

- CURRENT RATING : 1 A
- INSULATION RESISTANCE : >1000 M OHM min. (AT 500 V DC)
- DIELECTRIC WITHSTANDING VOLTAGE : AC 500 V min. (FOR 1 MINUTE)
- OPERATING TEMPERATURE : -25°C to 85°C
- CONTACT RESISTANCE : 15m OHM max.
- DIELECTRIC MATERIAL : PBT & GLASS-FIBER REINFORCED UL 94V-0
- SHELL MATERIAL : SPCC, NICKEL PLATED
- CONTACT MATERIAL : BRASS
- CONTACT PLATING : SELECTIVE GOLD over NICKEL
- WIRE SIZE : AWG 26 & 28 STRANDED, 1.27mm CONDUCTOR CENTRE FLAT CABLE
- CONNECTOR IS PART MARKED: [PART-NO. CONEC ABC]

RoHS compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY, WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm
				UNLESS OTHERWISE SPECIFIED TOLERANCE .00 ±0.25		
2 x g	Ä6247	27.07.2016	K.H.	2002	date	name
2 x f	Ä6008	03.06.2014	Lehmen	drawn	07.05.	Parei
6 x e	Ä4972	28.10.2013	Lehmen	appd.	07.05.	E. Mickenbecker
1 x d	Ä 2571	07.09.2006	Lehmen	norm		
2 x c	Ä 2568	30.08.2006	Lehmen	d-old		
3 x b	Ä 2561	24.08.2006	Lehmen			
a	Original					
rev.	description	date	name			

scale:	2:1	
material:	SEE SPECIFICATION	
title:	D-SUB MALE I.D.C. TYPE 9-37pos. for flat cable	
dwg no:	AutoCAD	DIN-A
	16K11FEA	3
part no:	SEE TABLE	
		sh: 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[301A10109X](#) [302A10089XR](#) [302A10089X-1](#) [DLS1XSSAG10X](#)