

4

3

2

1

used for: D-SUB COMBINATION

F

F

E

E

D

D

C





C

B

B

A

A



NOTES:


1. METALSHELLS: STEEL: TIN PLATED
2. INSULATOR: PBTP GF UL 94 V-0; GREEN
3. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance



1998	date	name
drawn	16.10.	Barcinski
appd.	16.10.	Mickenbecker
norm		
d-old		

CONEC®scale: 2:1
material: SEE NOTEStitle:
D-SUB COMBINATION MALE
2W2CP
WITHOUT CONTACTS

dwg no: AutoCAD/REL.13 DIN-A

13K1IJ8A

4
sh: 1/1

part no: 302W2CPXX99A10X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[302W2CPXX99A10X](#)