


D see data sheet cable

Technical specification:

Rated voltage: IEC 61076-2-101	4pos 250 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	≥ 100 M Ω
Pollution degree: IEC 60664-1	3/2
Degree of protection: DIN 40050-9	IP 69K, in mated condition
Temperature range: IEC 60664-1	-30°C ... +105°C
Mating cycles: IEC 60512-9a	≥ 100
Materials:	
Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	PP GF, UL 94
Sealing:	FPM
Coupling nut:	1.4404 stainless steel
Moulding body:	Thermoplastic elastomere, grey

Installation specification:

Recommended torque:	0,6 Nm
---------------------	--------

Contact assignment:


- 1) brown
- 2) white
- 3) blue
- 4) black

Part no:	Description:	Length L:	Cable:
43-10528	SAL - FB - 12 - RKW4 - 2 / P1	2m	PP, orange, 4x0,34mm ² Cable: 781-P13400
43-10529	SAL - FB - 12 - RKW4 - 3 / P1	3m	
43-10530	SAL - FB - 12 - RKW4 - 5 / P1	5m	
43-10531	SAL - FB - 12 - RKW4 - 10 / P1	10m	
43-xxxxx	SAL - FB - 12 - RKW4 - ... / P1	x	

Index: a 22.02.11 VF Ä3909
technical specification changed, part no.
cable in table added, data sheet modified

tolerance of cable: L $\leq$ 4m: L + 40mm
L > 4m: L + 1%

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH



dim. in mm

	date	name
drawn	08.03.07	Burschik
appd.	08.03.07	Mankopf

CONEC®

title:

**Female connector M12x1 angled,
FB**

dwg no:

43K1A089

part no:

see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[43-10531](#)