


1. METAL SHELLS: STEEL; min. 320μ" TIN
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
4. PLATING: min. 30μ" HARD GOLD OVER min. 50μ" NICKEL
5. CONNECTOR IS PART MARKED: PART NO: CONEC YWW
6. = CRITICAL DIMENSION: SPC

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.

				tolerance			
				2001	date	name	
				drawn	28.05.	Parei	
				appd.	28.05.	Mickenbecker	
				norm			
				d-old			
							
rev.	description	date	name				



scale:	2:1 (5:1)		
material:	SEE NOTES		
title:			
D-SUB COMBINATION MALE 24W7P SOLDER CUP			
dwg no:	AutoCAD 2000	DIN-A	
13K1A262A		3	
part no: 3024W7PCM99A10X		sh: 1/1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[3024W7PCM99A10X](#)