





NOTES:

1. METAL SHELLS: STEEL; TIN PLATED
2. INSULATORS: PBT GF, UL 94 V-0; GREEN
3. CONTACTS: COPPER ALLOY
4. PLATING: min. 30µ" HARD GOLD OVER min. 50µ" NICKEL
5. = CRITICAL DIMENSION: SPC

Directive 2002/95/EC
"RoHS"
Compliant

DO NOT ALTER CAD DRAWING BY HAND		tolerance		scale: 2:1 (5:1)	
OWNERSHIP AND COPYRIGHT OF CONEC GMBH		material:		SEE NOTES	
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.		NORTEL		title: D-SUB COMBINATION MALE	
rev.	description	date	name	21WA4P SOLDER CUP	
1			Barcinski		
2			Mickenbecker		
3					
4					
5					
6					
7					
8					
dwg no: 13K11M2A			[CAD/ REL:13 DIN-A 3 sh:1/1]		
product no: 321WA4PCMH99A10X					



used for: D-SUB COMBINATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[321WA4PCM99A10X](#)