







b) STRIPPING DIMENSION



plating	part no.
GOLD FLASH over NICKEL	131A10039X
30µin HARD GOLD over min. 50µin NICKEL	131C10039X
50µin HARD GOLD over min. 50µin NICKEL	131J10039X

pos	qty	description	material	plating
3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED
2	1	REAR SIDE	COPPER ALLOY	GOLD FLASH over NICKEL
1	1	MATING SIDE	COPPER ALLOY	SEE TABLE
partlist				
tolerance				
dim. in mm				
scale: 5:1				
material: see notes				
title:				
HIGH POWER CONTACT MALE				
SOLDER CUP 30A				
D-SUB COMBINATION				
dwg no:				DIN-A3
13K11C9A				sh: 1
part no:				b) see table

Directive 2011/65/EU RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

4 x b	Ä4657	20.02.2013	K.H.
a	Original		
rev.	description	date	name

date	name
23.03.98	Barcinski
23.03.98	Mickenbecker
norm	d-old

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[131J10039X](#)