




POS.	A -0.76	B +0.25	C	D -0.3	PART NO.
9	31.19	16.79	25.00 $\begin{smallmatrix} +0.12 \\ -0.13 \end{smallmatrix}$	6.12	241A15140X
15	39.52	25.12	33.30 $\begin{smallmatrix} +0.15 \\ -0.1 \end{smallmatrix}$	6.12	241A15150X
37	69.70	55.30	63.50 ± 0.13	5.99	241A15170X



NOTES:

1. RoHS COMPLIANT
2. SUITABLE FOR WAVE SOLDERING
3. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
4. INSULATORS: HIGH TEMPERATURE PLASTIC UL 94 V-0, BLACK
5. CONTACTS: COPPER ALLOY
PLATING: 8pin HARD GOLD OVER min. 50µin NICKEL
6. THREADED SPACER CLIP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: Ø3.1±0.1; PCB THICKNESS 1.6mm
7. COLLAR: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
8. P.C.B. HOLE DRILLINGS ON SHEET 2
9. CAPACITANCE: 1300pF ±20%
10. DIELECTRIC WITHSTANDING VOLTAGE: 424 VDC
11. MAXIMUM TORQUE VALUE FOR THREAD: 6in.LB
12. CONNECTOR IS PART MARKED: **PART-NO. CONEC ABC**

RoHS compliant




APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

1 x c	Ä 3200	27.11.08	Petker	d-old
4 x b	Ä 3194	24.11.08	Petker	
a	Origin			
rev.	description	date	name	

tolerance	dim. in mm
1998	date
drawn	08.05. Barcinski
appd.	08.05. Mickenbecker
norm	DIN 41652

scale:	2:1 (5:1)
material:	SEE NOTES
title: D-SUB FILTER MALE P-TYP 9-37pos. PIN 5.8mm WITH THREADED SPACER CLIP	
dwg no:	AutoCAD 2000 DIN-A
24K11Y9A	
part no:	SEE TABLE



APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
4 x b	Ä 3194	24.11.2008	Petker
a	Origin		

tolerance	dim. in mm
1998	date
drawn	08.05.
appd.	08.05.
norm	DIN 41652
d-old	

scale:	2:1
material:	SEE SHEET 1
title:	P.C.B. HOLE DRILLINGS D-SUB FILTER MALE P-TYP 9-37pos. PIN 5.8mm WITH THREADED SPACER CLIP
dwg no:	AutoCAD 2006
part no:	SEE SHEET 1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[241A15140X](#)