

4




3

2


1

used for:

SEE NOTE 8



P.C.B.-HOLE DRILLINGS




RoHS compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	


NOTES:

1. INSULATOR: PBT 20% GF
2. CONTACTS: COPPER ALLOY; GOLD PLATED
3. WITHSTANDING VOLTAGE: 1000V DC OR AC PEAK
4. CURRENT RATING: 1A
5. CONTACT RESISTANCE: 20mOHM
6. INSULATION RESISTANCE: 5000MOhm at 100V
7. LIFE: 50 MATING CYCLES
8. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		
				2018	date	name
				drawn	23.07.	Lehmenkühler
				appd.	23.07.	Henneboel
				norm	DIN 41651	
				d-old		
a	Original					
rev.	description	date	name			

CONEC®



scale: 2:1
material: SEE NOTES

title:
LOW PROFILE HEADER
10-50pos.
with right angle solder pins

dwg no: AutoCAD DIN-A
14K1A041 4
sh: 1/1

part no: SEE TABLE

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[141A12069X](#)