








NOTES:

1. RoHS COMPLIANT
2. SUITABLE FOR WAVESOLDERING
3. METALSHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
4. INSULATORS: HIGH TEMPERATURE PLASTIC UL 94 V-0, BLACK
5. CONTACTS: COPPER ALLOY
PLATING: 8µm HARD GOLD over min. 50µm NICKEL
CONTACT TAILS PRETINNED
6. METAL BRACKETS: ZINC DIE CAST; 300µm COPPER/40-120µm NICKEL/120-200µm TIN
7. THREADED INSERTS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
8. CAPACITANCE: 2 x 830pF ± 20%
9. DIELECTRIC WITHSTANDING VOLTAGE: 300 VDC
10. P.C.B. HOLE DRILLINGS ON SHEET 2
11. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
12. CONNECTOR IS PART MARKED: **24-500673 CONEC ABC**

Directive 2002/95/EC
RoHS
Compliant


APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	


THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

Customer Specific Product				tolerance		 dim. in mm
				date	name	
				drawn	04.05.09	Sonnenberg
				appd.	04.05.09	Koch
				norm	DIN 41652	
				d-old		
a	Origin					
rev.	description	date	name			

scale:	2:1 (5:1)	
material:	SEE NOTES	
title:	D-SUB π Filter Male 90° 37pos., 0,590inch threaded insert and metal bracket	
dwg no:	Inventor 10	DIN-A3
	24K1A1176	sh: 1
part no:	24-500673	



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				tolerance			 dim. in mm	scale: 2:1		
									material: SEE SHEET 1		
						date	name	title: P.C.B. HOLE DRILLINGS D-SUB π Filter Male 90° 37pos., 0,590inch threaded insert, metal bracket and snap			
					drawn	04.05.09	Sonnenberg				
					appd.	17.06.08	Mickenbecker				
					norm	DIN 41652					
					d-old						
								dwg no:		Inventor 10	DIN-
	a	Origin						24K1A1176		A4	
	rev.	description	date	name				part no: SEE SHEET 1		sh: 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[24-500673](#)