


4-40 UNC

16,3




41,8

39,5

Ø11

25

32,9



NOTES: (c)

1. HOOD + COVER: PBT UL 94 V-0; BLACK
2. CABLE STRAIN RELIEF: STEEL; NICKEL PLATED
3. PRESS INSERT: ABS UL 94 V-0; BLACK
4. SHORT SCREWS: STEEL; NICKEL PLATED
5. LENS HEAD SCREWS: STEEL; NICKEL PLATED

TECHNICAL DATA: (b)

- TEMPERATURE RANGE: -40°C to + 125°C



CABLE STRAIN RELIEF (1x)




LENS HEAD SCREW (4x)



SHORT SCREW (2x)



PRESS INSERT (1x)



RoHS compliant

(b)

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
5 x c	A5607	14.04.15	M.H.
3 x b	A5307	25.08.14	E.Mick.
a	Original		

tolerance	dim. in mm
date	name
drawn 08.07.2002	Parei
appd. 08.07.2002	E. Mickenbecker
norm	

CONEC

scale: 2:1
material: SEE NOTES
title: PLASTIC HOOD 9pos. with straight cable exit
dwg no: 16K1A707
part no: 165X13369X / 600X10009XS

(b)

(c)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[165X13369X](#)