



TOP VIEW
DRAWN WITHOUT
CABLE BUSHING

Pos.	A	B	C	D	E	ØF	G ^{+0.2}	H	Part NO. Bulk package	Part NO. Single package
9	31.7	25.0	30.0	32.7	15.0	5.0	9.0	9.0	165X17359X	165X17359XE
15	40.0	33.3	32.0	34.7	15.0	5.0	9.0	9.0	165X17369X	165X17369XE
25	53.7	47.0	35.0	37.7	15.0	7.0	12.2	10.0	165X17379X	165X17379XE
37	70.2	63.5	41.0	43.7	15.0	7.0	13.5	11.0	165X17389X	165X17389XE
50	67.8	61.1	41.0	43.7	17.7	9.3	15.3	12.7	165X17399X	165X17399XE

G:\RoHS_Compliant_gross_0001.jpg

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

NOTES:

1. CASE: ZINC DIE CAST; NICKEL PLATED
2. JACK SCREW: COPPER ALLOY; NICKEL PLATED
3. CABLE BUSHING: TPE
4. CABLE STRAIN RELIEF: STEEL; NICKEL PLATED
5. ATTENUATION FACTOR >60dB BETWEEN 300 MHz AND 900 MHz

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND	tolerance		dim. in mm	scale:	1:1
				material:	SEE NOTES
	2007	date	name	title: METAL HOOD 9-50pos. EMI / RFI SHIELDING with straight cable exit and jack screws M3	
	drawn	13.11.	Lehmenkühler		
	appd.	13.11.	Kühle		
	norm				
d-old			dwg no:	AutoCAD 2006	DIN-A
a	Origin			16K1A2177	
rev.	description	date	name	part no: SEE TABLE	

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[165X17359X](#) [165X17389X](#) [165X17359XE](#) [165X17379X](#) [165X17399X](#) [165X17369X](#)