



No. of pos.	A	B	C	D	ØE _{max.}	Part No. Single package	Part No. Bulk package
9	31.2	25.0	31.8	15.6	8.0	165X11869XE	165X11869X
15	39.5	33.3	37.0	15.6	8.0	165X11879XE	165X11879X
25	53.2	47.0	42.2	15.6	10.0	165X11889XE	165X11889X
37	69.7	63.5	42.2	15.6	10.0	165X11899XE	165X11899X
50	67.3	61.1	42.2	18.5	12.5	165X11909XE	165X11909X

NOTES:

- ⓑ 1. HOOD: PC UL 94 V-0; GREY
- ⓑ 2. HOOD PLUG: PC UL 94 V-0; GREY
3. JACKSCREW: BRASS; NICKEL PLATED
4. SCREW FOR STRAIN RELIEF: STEEL; NICKEL PLATED
5. COVER SCREW: STEEL; NICKEL PLATED
6. STRAIN RELIEF: STEEL; NICKEL PLATED

Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
2 x c	Ä 2795	04.09.07	Lehmen
3 x b	Ä 2545	04.08.06	HS
a	Origin		

tolerance	dim. in mm
2006	date
drawn	06.02. Lehmenkübler
appd.	07.02. Mickenbecker
norm	
d-old	

scale:	1:1
material:	SEE NOTES
title:	
PLASTIC HOOD	
9pos. with top cable exit	
15-50pos. with top and side cable exit	
dwg no:	AutoCAD 2004 DIN-A
16K1A1734	
part no:	SEE TABLE
sh: 1/1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[165X11909X](#)