

4


3

2

1

used for:

D-SUB



PLATING / CONTACT AREA

PART-NO.


GOLD FLASH over NICKEL

162A11819X

20µin HARD GOLD over min. 50µin NICKEL

162B11819X

## STRIPPING DIMENSIONS



RoHS compliant

## NOTES:

Material: Phosphor Bronze

Finish: See Table

Temperature Range: -55°C to +125°C

Rated Current: 7.5A

Contact Resistance: ≤ 10mΩ

Length of Reel - big reel wheeled left: 10000 contacts


Crimping: Use Crimp Tool 360X10079X for loose contact

THIS DRAWING MAY NOT BE COPIED OR  
REPRODUCED IN ANY WAY, AND MAY NOT  
BE PASSED ON TO A THIRD PARTY WITHOUT  
WRITTEN PERMISSION.  
OWNERSHIP AND COPYRIGHT OF CONEC GmbH  
DO NOT ALTER CAD DRAWING BY HAND

finish:

SEE TABLE

tolerance



scale:

5:1

material:

SEE NOTES

title:

SOCKET CONTACT  
CRIMP AWG 24-20  
(big reel wheeled left)

dwg no:

AutoCAD

DIN-A

16K1A3708

4

sh: 1/1

part no:

SEE TABLE

a

Original

rev.

description

date

name

**CONEC**®

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[162A11819X](#)