






Shellsize	A	B	C	Ø D	E	F	* G ± 1	Cable Ø	Part-No.
1	40	25	20 A/F	23	36	21	54,3	7 - 9	15-004710
2	48	33,3	22 A/F	25	36	21	54,6	9 - 11	15-004720
3	62	47,04	24 A/F	27	44	21	67,7	10 - 12	15-004730
4	78	63,5	28 A/F	31	53	25,2	77,2	14 - 16	15-004740
5	75,6	61,1	28 A/F	31	53	23,8	77,2	14 - 16	15-004750

(1 : 1)



* COMPLETELY TIGHTENED

NOTES:

- MATERIALS:
HOOD: PBT GF UL94 V-0 BLACK
FRONTSEALING: SILICONE VMQ BLUE
SCREW: STAINLESS STEEL
O-RING: NBR BLACK
- TEMPERATURE RANGE: -30°C TO +90°C
- RECOMMENDED TORQUE FOR SCREW:
35Ncm (3.1 in.LB)
MAX. TORQUE: 68Ncm (6 in.LB)
- SINGLE PACKED

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND					tolerance ± 0,3 unless otherw. specified		 dim. in mm	scale: 1,5:1 (2:1)	
								material: SEE NOTES	
						date	name	title: WATER RESISTANT D-SUB HOOD 9-15 POS. SHORT SCREW 4-40UNC STAINLESS STEEL	
					drawn	25.09.12	Huether		
					appd.	11.10.12	Kuehle		
					norm				
					d-old			dwg no: 15K1A1153 part no: SEE TABLE	
									
	a	Origin						DIN-A3	
rev.	description	date	name				sh: 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[15-004720](#) [15-004740](#) [15-004710](#) [15-004730](#) [15-004750](#)