





used for: RJ 45



Directive 2002/95/EC
„RoHS“
Compliant



P.C.B. HOLE DRILLINGS



NOTES:

1. HOUSING MATERIAL: GLASS FILLED NYLON 46, BLACK
2. SHIELD MATERIAL: 0.2mm THICK COPPER ALLOY
3. CONTACT MATERIAL: 0.35mm THICK COPPER ALLOY
4. MATING AREA PLATING: min. 50µ" GOLD over min. 30µ" NICKEL
5. SOLDER TAILS PLATING: min. 90µ" TIN/LEAD over min. 30µ" NICKEL
6. LED: GREEN AND YELLOW
7. INTERNAL CIRCUIT PER PORT SEE 39K1A041

APPROVAL * FREIGABE * DEBLOCKAGE * AUTOR/ZACON * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCKAGE * AUTOR/ZACON * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance		 dim. in mm
2002	date	
drawn	27.11.	name
appd.	27.11.	Kühle
norm		
d-old		
		

scale:	2:1	
material:	SEE NOTES	
title:	RJ 45 MAGNETIC MODULAR JACK 1. PORT SMT-TERMINATION fully screened, with LED	
dwg no:	AutoCAD 2000	DIN-A
	39K1A049	3
part no:	RJ45SJS11AC010X	
		sh: 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[RJ45SJS11AC010X](#)