



Technical specification:

Rated voltage: IEC 60664-1	300 V
Overvoltage category: IEC 60664-1	2
Overvoltage: IEC 60664-1	2,7 kV
Current rating: IEC 60512-3 at 40°C	0,75mm ² 8 A 1,5mm ² 10 A
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 68, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100
Termination:	crimped

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU, UL 94
Coupling nut:	CuZn, nickel plated
Moulding body:	TPU, UL 94, grey

Contact assignment:

- 1) brown
- 2) white
- 3) blue
- 4) black

Part no:	Description:	Length L:	Cable:
41-01048	SAL - 7/8 - RKW4 - 2 / A3	2m	PVC, UL 2464, grey, 4x0,75mm ² Cable: 781-A37400
41-01049	SAL - 7/8 - RKW4 - 3 / A3	3m	
41-01050	SAL - 7/8 - RKW4 - 5 / A3	5m	
41-01041	SAL - 7/8 - RKW4 - 10 / A3	10m	
41-xxxxx	SAL - 7/8- RKW4 - ... / A3	x	
41-01145	SAL - 7/8 - RKW4 - 2 / A3 / 150	2m	PVC, UL 2464, grey, 4x1,50mm ² Cable: 781-A3840G
41-01146	SAL - 7/8 - RKW4 - 3 / A3 / 150	3m	
41-01147	SAL - 7/8 - RKW4 - 5 / A3 / 150	5m	
41-01148	SAL - 7/8 - RKW4 - 10 / A3 / 150	10m	
41-xxxxx	SAL - 7/8 - RKW4 - ... / A3 / 150	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: c 02.09.10 KH Ä3736 technical specification changed, part no. cable in table added, neutral line added		 dim. in mm		title: Female connector 7/8" angled	
			date	name		
	tolerance of cable:	L ≤ 4m: L + 40mm L > 4m: L + 1%	drawn	10.10.07	Franz	dwg no: 41K1A305
			appd.	10.10.07	Mankopf	
	general tolerance:	0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm				part no: see table
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH						

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[41-01147](#) [41-01049](#) [41-01048](#) [41-01145](#) [41-01050](#) [41-01148](#) [41-01146](#)