





Contact assignment:


1	black
2	blue
PE	green-yellow
4	brown
5	white

Technical specification:

Rated voltage: IEC 60664-1	300 V
Overvoltage category: IEC 60664-1	2
Overvoltage: IEC 60664-1	2,7 kV
Current rating: IEC 60512-3 at 40°C	0,75mm ² 1,5mm ² 8 A 10 A
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 68, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100
Termination:	crimped

Materials:


Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU, UL 94
Coupling screw:	CuZn, nickel plated
Moulding body:	TPU, UL 94, grey



Part no:	Description:	Length L:	Cable:
41-01092	SAL - 7/8 - RSW4PE - 2 / K1	2m	TPU, UL 20549, black, 5x0,75mm ² Cable: 781-K17500
41-01093	SAL - 7/8 - RSW4PE - 3 / K1	3m	
41-01094	SAL - 7/8 - RSW4PE - 5 / K1	5m	
41-01095	SAL - 7/8 - RSW4PE - 10 / K1	10m	
41-xxxxx	SAL - 7/8 - RSW4PE - ... / K1	x	
41-01189	SAL - 7/8 - RSW4PE - 2 / K1 / 150	2m	TPU, UL 20549, black, 5x1,50mm ² Cable: 781-K18500
41-01190	SAL - 7/8 - RSW4PE - 3 / K1 / 150	3m	
41-01191	SAL - 7/8 - RSW4PE - 5 / K1 / 150	5m	
41-01192	SAL - 7/8 - RSW4PE - 10 / K1 / 150	10m	
41-xxxxx	SAL - 7/8 - RSW4PE - ... / K1 / 150	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND
Directive 2002/95/EC RoHS compliant

Index: b 03.09.10 KH A3736 technical specification changed, part no. cable in table added, neutral line added		 dim. in mm		title: Male connector 7/8" angled	
			date		
tolerance of cable:	L <= 4m: L + 40mm L > 4m: L + 1%	drawn	10.10.07	Franz	dwg no:
		appd.	10.10.07	Mankopf	
general tolerance:	0 ± 0,50mm			41K1A304	
	0,0 ± 0,25mm				
	0,00 ± 0,10mm			part no: see table	
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[41-01190](#) [41-01092](#) [41-01189](#) [41-01095](#) [41-01093](#) [41-01192](#) [41-01094](#) [41-01191](#)