






Technical specification:

Rated voltage: IEC 61076-2-101	4pos 250 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	≥100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 65, in mated condition
Temperature range: IEC 60664-1	+100°C - 30.000 h +125°C - 8.000 h +150°C - 2.000 h
Mating cycles: IEC 60512-9a	≥100

Materials:

Contact:	CuZn, CuBe
Contact plating:	Nickel, gold plated
Contact carrier:	PBT GF, UL 94
Sealing:	FPM
Coupling nut/ screw:	CuZn, nickel plated
Moulding body:	Thermoplastic elastomere, grey

Installation specification:

Recommended torque:	0,6 Nm
---------------------	--------

Contact assignment:

1) brown	■
2) white	■
3) blue	■
4) black	■

D see data sheet cable

Part no:	Description:	Length L:	Cable:
43-10908	SAL - HT - 12 - RKW4 - RS4 - 0,3 / S1	0,3m	TPE, black, 4x0,34mm ² Cable: 781-S13400
43-10909	SAL - HT - 12 - RKW4 - RS4 - 0,6 / S1	0,6m	
43-10910	SAL - HT - 12 - RKW4 - RS4 - 1,5 / S1	1,5m	
43-10911	SAL - HT - 12 - RKW4 - RS4 - 3,0 / S1	3m	
43-xxxxx	SAL - HT - 12 - RKW4 - RS4 - ... / S1	x	

DO NOT ALTER CAD DRAWING BY HAND	Directive 2002/95/EC RoHS compliant	Index: b 16.02.11 VF Ä3909 technical specification changed, part no. cable in table added, data sheet modified
		tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%
		THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
		OWNERSHIP AND COPYRIGHT OF CONEC GmbH

dim. in mm		
	date	name
drawn	14.03.07	Burschik
appd.	14.03.07	Mankopf



title:	Connecting cable M12x1, HT, female connector angled - male connector axial
dwg no:	43K1A450
part no:	see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-10908](#) [43-10909](#) [43-10910](#) [43-10911](#)