






D see data sheet cable

Technical specification:

Rated voltage: IEC 61076-2-101	4pos 250 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: DIN 40050-9	IP 69K, in mated condition
Temperature range: IEC 60664-1	-30°C ... +105°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	PP GF, UL 94
Coupling screw:	1.4404 stainless steel
Moulding body:	Thermoplastic elastomer, grey

Installation specification:

Recommended torque:	0,6 Nm
---------------------	--------

Contact assignment:

1	brown
2	white
3	blue
4	black

Part no:	Description:	Length L:	Cable:
43-10520	SAL - FB - 12 - RS4 - 2 / P1	2m	PP, orange, 4x0,34mm ² Cable: 781-P13400
43-10521	SAL - FB - 12 - RS4 - 3 / P1	3m	
43-10522	SAL - FB - 12 - RS4 - 5 / P1	5m	
43-10523	SAL - FB - 12 - RS4 - 10 / P1	10m	
43-xxxxx	SAL - FB - 12 - RS4 - ... / P1	x	

DO NOT ALTER CAD DRAWING BY HAND	Directive 2002/95/EC RoHS compliant	Index: a 21.02.11 VF Ä3909 technical specification changed, part no. cable in table added, data sheet modified
		tolerance of cable: $L \leq 4\text{m}: L + 40\text{mm}$ $L > 4\text{m}: L + 1\%$
		THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
		OWNERSHIP AND COPYRIGHT OF CONEC GmbH

dim. in mm		
	date	name
drawn	16.03.07	Mankopf
appd.	16.03.07	Fromm

title:		Male connector M12x1 axial, FB
dwg no:		43K1A061
part no:		see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-10522](#) [43-10520](#) [43-10521](#) [43-10523](#)