







Technical specification:

Rated voltage: IEC 61076-2-101	6pos 30 V
Current rating: IEC 61076-2-101	2 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Sealing:	FPM
Coupling nut/ screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:

Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220

Contact assignment:

1) brown	5) black
2) white	6) grey
3) blue	7) pink

D see data sheet cable

Part no:	Description:	Length L:	Cable:
43-14689	SAL - 12 - RKW6 - RSW6 - 0,3 / A1 / A1090	0,3m	PVC, grey, 6x0,25mm ² Cable: 781-A12600
43-14690	SAL - 12 - RKW6 - RSW6 - 0,6 / A1 / A1090	0,6m	
43-14691	SAL - 12 - RKW6 - RSW6 - 1,5 / A1 / A1090	1,5m	
43-14692	SAL - 12 - RKW6 - RSW6 - 3,0 / A1 / A1090	3m	
43-xxxxx	SAL - 12 - RKW6 - RSW6 - ... / A1 / A1090	x	

DO NOT ALTER CAD DRAWING BY HAND	Directive 2002/95/EC RoHS compliant
tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%	
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	

dim. in mm	date	name
drawn	19.01.11	Franz
appd.	19.01.11	Mankopf
CONEC®		

title:	Connecting cable M12x1, female connector angled - male connector angled
dwg no:	43K1A1299
part no:	see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-14689](#) [43-14691](#) [43-14692](#) [43-14690](#)