


D see data sheet cable

Technical specification:

Rated voltage: IEC 61076-2-101	6pos 30 V
Current rating: IEC 61076-2-101	2 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Coupling screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey


Installation specification:

Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220

Contact assignment:

1 brown	4 black
2 white	6 grey
3 blue	7 pink

Part no:	Description:	Length L:	Cable:
43-14460	SAL - 12 - RSW6 - 2 / A1 / A1090	2m	PVC, grey, 6x0,25mm ² Cable: 781-A12600
43-14461	SAL - 12 - RSW6 - 3 / A1 / A1090	3m	
43-14462	SAL - 12 - RSW6 - 5 / A1 / A1090	5m	
43-14463	SAL - 12 - RSW6 - 10 / A1 / A1090	10m	
43-xxxxx	SAL - 12 - RSW6 - ... / A1 / A1090	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	 dim. in mm		title:	
			Male connector M12x1 angled	
	tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%		dwg no:	
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm		43K1A1239	
			part no: see table	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-14463](#) [43-14461](#) [43-14460](#) [43-14462](#)