




Technical specification:

Technische Daten:


Rated Voltage/ Bemessungsspannung: IEC 61076-2-101	4 pos / 4pol 250 V	5 pos / 5pol 60 V
Current rating/ Strombelastbarkeit: IEC 61076-2-101	4 A at / bei 40 °C	
Insulation resistance/ Isolationswiderstand: IEC 60512	>=100 MΩ	
Pollution degree/ Verschmutzungsgrad: IEC 60664-1	3/2	
Degree of protection/ Schutzart: IEC 60529	IP 67, in mated condition/ im gesteckten Zustand	
Temperature range/ Umgebungstemperatur:	-40 °C ... +130 °C static / fest	
Mating cycles/ Steckzyklen: IEC 60512-9a	>=100	

Materials/




Werkstoffe:

Contact/ Kontakt:	CuZn, Ni b / Au 0,2 gal.	
Contact carrier/ Kontaktträger:	PA GF, UL 94 V-0	
Sealing/ Dichtung	FPM	

A
4pos / 4pol




A
5pos / 5pol



Conec part no./ Conec Art.-Nr.:	Description/ Bezeichnung:	Pos/ Pol	Construction/ Ausführung
43-01336	SAL - 12 - ES4 - L	4	without sealing/ ohne O-Ring
43-01337	SAL - 12 - ES5.1 - L	5	without sealing/ ohne O-Ring
43-01338	SAL - 12 - ESO4 - L	4	with sealing/ mit O-Ring
43-01339	SAL - 12 - ESO5.1 - L	5	with sealing/ mit O-Ring

general tolerance/
Allgemeintoleranz:

0	± 0,50 mm
0,0	± 0,25 mm
0,00	± 0,10 mm
*	± 1,5 °



dim. in mm

drawn/
gez.

13.10.2008

appd./
gepr.:

27.10.2008



Name

Fromm

Mankopf

Male socket M12x1,
with soldering version
Einbaustecker M12x1 mit Lötanschluß

Index: h 10.12.19 rch Ä19-0454

Status: Freigegeben

RoHS & REACH compliant/ konform

scale/ Maßstab:

CONEC®

dwg no /
Z.-nr.:

43K1A754

DIN-
A4

1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-01339](#) [43-01338](#) [43-01337](#) [43-01336](#)