


D-SUB HIGH DENSITY

Solder cup – Stamped contacts – For wire size AWG 22





RoHS compliant – CSA listed, File No.: LR 115000-1 – UL listed, File No.: E202784

SOCKET CONNECTOR



No. of pos.	A -0.76	B -0.25	C
15	31.19	16.46	25.00 +0.12
26	39.52	24.79	33.30 +0.15
44	53.42	38.50	47.04 +0.13
62	69.70	54.96	63.50 +0.13
78	67.31	52.55	61.10 +0.14

Mounting style: Through-hole




78 pos. = Dim. in (_)

DESCRIPTION



- Suitable for wire size **AWG 22**
- Mounting style:
with through-hole Ø .118" / 3 mm
- Quality class 3 (other quality classes on request)
- Shell: Steel tin plated

PLUG CONNECTOR



No. of pos.	A -0.76	B +0.25	C	D -0.3
15	31.19	16.79	25.00 +0.12	6.12
26	39.52	25.12	33.30 +0.15	6.12
44	53.42	38.84	47.04 +0.13	5.99
62	69.70	55.30	63.50 +0.13	5.99
78	67.31	52.68	61.10 +0.14	5.99

Mounting style: Through-hole



78 pos. = Dim. in (_)

ORDER DATA

SOCKET CONNECTOR		
No. of pos.	Mounting style	Part Number
15	Through-hole	302 A 10129 X
26	Through-hole	302 A 10139 X
44	Through-hole	302 A 10149 X
62	Through-hole	302 A 10159 X
78	Through-hole	302 A 11329 X

PLUG CONNECTOR		
No. of pos.	Mounting style	Part Number
15	Through-hole	301 A 10129 X
26	Through-hole	301 A 10139 X
44	Through-hole	301 A 10149 X
62	Through-hole	301 A 10159 X
78	Through-hole	301 A 11019 X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)
[302A11329X](#)