


D-SUB STANDARD

Crimp body (without contacts) – For wire size AWG 24...20 and AWG 28...24




RoHS compliant – CSA listed, File No.: LR 115000-1 – UL listed, File No.: E202784

SOCKET CONNECTOR




No. of pos.	A -0.76	B -0.25	C	D -0.3
09	31.19	16.46	25.00 +0.12	6.12
15	39.52	24.79	33.30 +0.15	6.12
25	53.42	38.50	47.04 +0.13	5.99
37	69.70	54.96	63.50 +0.13	5.99
50	67.31	52.55	61.10 +0.14	5.99

Mounting style: Through-hole



50 pos. = Dim. in (_)


Mounting style: Threaded insert



DESCRIPTION


- For machined and stamped contacts, AWG 24...20 and AWG 28...24
- Mounting styles:
 - with through-hole, Ø .118" / 3 mm
 - with 4-40 UNC or M3 threaded insert
- Shell: Steel tin plated (brass tin plated or stainless steel available on request)

PLUG CONNECTOR




No. of pos.	A -0.76	B -0.25	C	D -0.3
09	31.19	16.79	25.00 +0.12	6.12
15	39.52	25.12	33.30 +0.15	6.12
25	53.42	38.84	47.04 +0.13	5.99
37	69.70	55.30	63.50 +0.13	5.99
50	67.31	52.68	61.10 +0.14	5.99

Mounting style: Through-hole



50 pos. = Dim. in (_)

Mounting style: Threaded insert



ORDER DATA

SOCKET CONNECTOR		
No. of pos.	Mounting style	Part Number
09	Through-hole	164X 11769 X
15	Through-hole	164X 11779 X
25	Through-hole	164X 11789 X
37	Through-hole	164X 11799 X
50	Through-hole	164X 11809 X
09	4-40 UNC Threaded insert	DSS 1XSXXG04 X
15	4-40 UNC Threaded insert	DSS 2XSXXG04 X
25	4-40 UNC Threaded insert	DSS 3XSXXG04 X
37	4-40 UNC Threaded insert	DSS 4XSXXG04 X
50	4-40 UNC Threaded insert	DSS 5XSXXG04 X
09	M3 Threaded insert	DSS 1XSXXG03 X
15	M3 Threaded insert	DSS 2XSXXG03 X
25	M3 Threaded insert	DSS 3XSXXG03 X
37	M3 Threaded insert	DSS 4XSXXG03 X
50	M3 Threaded insert	DSS 5XSXXG03 X

PLUG CONNECTOR		
No. of pos.	Mounting style	Part Number
09	Through-hole	163X 10019 X
15	Through-hole	163X 10029 X
25	Through-hole	163X 10039 X
37	Through-hole	163X 10049 X
50	Through-hole	163X 10059 X
09	4-40 UNC Threaded insert	DSS 1XPXXG04 X
15	4-40 UNC Threaded insert	DSS 2XPXXG04 X
25	4-40 UNC Threaded insert	DSS 3XPXXG04 X
37	4-40 UNC Threaded insert	DSS 4XPXXG04 X
50	4-40 UNC Threaded insert	DSS 5XPXXG04 X
09	M3 Threaded insert	DSS 1XPXXG03 X
15	M3 Threaded insert	DSS 2XPXXG03 X
25	M3 Threaded insert	DSS 3XPXXG03 X
37	M3 Threaded insert	DSS 4XPXXG03 X
50	M3 Threaded insert	DSS 5XPXXG03 X

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[DSS5XSFAA54X](#) [DSS5XPFAA50X](#) [DSS5XPFAA54X](#) [164A10289X](#)