



D-SUB HIGH DENSITY – IP67 SOLID BODY

Solder pin – Angled – .362"/11.7 mm – Precision machined contacts – Metal bracket




RoHS compliant


SOCKET CONNECTOR




No. of pos.	A	B2 ± 0.25	C	D
15	39.40 ± 0.3	16.46 ± 0.13	25.00 ± 0.12	21.1 ± 0.3
26	47.70 ± 0.3	24.79 ± 0.13	33.32 ± 0.12	21.1 ± 0.3
44	61.40 ± 0.3	38.50 ± 0.13	47.04 ± 0.12	21.1 ± 0.3
62	78.00 ± 0.3	54.96 ± 0.13	63.50 ± 0.12	21.1 ± 0.3
78	75.60 ± 0.3	52.55 ± 0.11	61.10 ± 0.14	23.9 ± 0.3



15-62 pos



78 pos




() = 78 pos.


DESCRIPTION

- Mounting style:
Mounting bracket, 4-40 UNC PCB clip including hex locking bolt
- Quality class 3 (also available in quality class 1)
- One-piece zinc die-cast nickel plated shell
- IP67 for harsh environments, pressure-proof up to 1.45 PSI
- Higher protection on request


PLUG CONNECTOR




No. of pos.	A	B1	C	D	E
15	39.40 ± 0.3	16.81 ± 0.23	25.00 ± 0.12	21.1 ± 0.3	6.00 ± 0.12
26	47.70 ± 0.3	25.14 ± 0.23	33.32 ± 0.12	21.1 ± 0.3	6.00 ± 0.12
44	61.40 ± 0.3	38.86 ± 0.23	47.04 ± 0.12	21.1 ± 0.3	5.99 ± 0.3
62	78.00 ± 0.3	55.32 ± 0.23	63.50 ± 0.12	21.1 ± 0.3	5.99 ± 0.3
78	75.60 ± 0.3	52.80 ± 0.12	61.10 ± 0.11	23.9 ± 0.3	5.99 ± 0.1



15-62 pos



78 pos



() = 78 pos.

ORDER DATA

SOCKET CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
15	Mounting bracket / PCB clip	15-002243
26	Mounting bracket / PCB clip	15-002253
44	Mounting bracket / PCB clip	15-002263
62	Mounting bracket / PCB clip	15-002273
78	Mounting bracket / PCB clip	15-002283

PLUG CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
15	Mounting bracket / PCB clip	15-002193
26	Mounting bracket / PCB clip	15-002203
44	Mounting bracket / PCB clip	15-002213
62	Mounting bracket / PCB clip	15-002223
78	Mounting bracket / PCB clip	15-002233

PCB clip .122"/3.1 $\pm$.004"/0.10 mm hole diameter and .063"/1.6 mm circuit board thickness
For different PCB thickness please contact factory.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[15-002223](#) [15-002273](#) [15-002283](#)