


(b)

POS.	A	B	C	D max. cable ϕ	E	F	Part No. Single package
9	32.0	25.0	36.7	6.3	15.5	16.5	165X11239XE
15	40.0	33.3	38.2	8.0	15.5	16.5	165X11249XE
25	54.2	47.0	42.2	10.5	15.5	16.5	165X11259XE
37	70.6	63.5	47.2	11.5	15.5	16.5	165X11269XE

NOTES:

- HOOD + COVER: ABS UL 94 V-0, BLACK
- BLIND PLUG: ABS UL 94 V-0, BLACK
- CABLE STRAIN RELIEF: STEEL; NICKEL PLATED
- COUNTERSUNK HEAD SCREW: STEEL; NICKEL PLATED
- JACK SCREW: BRASS; NICKEL PLATED

Directive 2002/95/EC
"RoHS"
Compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance			
				2006	date	name	
				drawn	07.02.	Lehmenkühler	
				appd.	07.02.	Mickenbecker	
				norm			
				d-old			
1 x b	Ä 2607	21.11.2006	Lehmen				
a	Origin						
rev.	description	date	name				

CONEC®

AutoCAD 2004
DIN-A
4
sh: 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

165X11269XE