





Part-no. as per finish		
raw (RoHS compliant)	yellow chromate	2 - 4µm gal. Ni (RoHS compliant)
740-342400	740-342450	740-342470

NOTES:

1. Part is splint and burr free
2. Excellent adhesion of surface to the base material
3. Threaded core dimension M3: 2.46 +0.1mm
4. Go - no go - gauge: M3-6H (Internal thread)
M3-6g (External thread)
5. Torque value for thread = min. 90 Ncm

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

finish: see table				tolerance		 dim. in mm
					date	name
				drawn	30.10.97	Barcinski
				appd.	30.10.97	Mickenbecker
				norm		
4 x c	Ä6129	17.05.16	Lehm.	d-old		
1 x b	Ä2590	19.10.06	Lehm.			
a	Original					
rev.	description	date	name			

CONEC®

scale:	5:1	
material:	(b) STEEL 1.0737 JIS SUM 25	
title:	HEX BOLT M3 / M3 13mm long	
dwg no:	740FEN0A	DIN-A4
part no:	see table	
		sh: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[740-342470](#)