

4


3

2

1

used for:

D-SUB



material	finish	part-no.
Steel	2 µm Ni	740-366770
Stainless Steel 1.4305 JIS SUS 303	-----	740-366760

## NOTES:

- Part is splint and burrfree
- Excellent adhesion of surface to the base material
- Threaded core dimension 4-40UNC: 2.157+-0.1
- Test equipment measurement: 4-40UNC - 2A




THIS DRAWING MAY NOT BE COPIED OR  
REPRODUCED IN ANY WAY, AND MAY NOT  
BE PASSED ON TO A THIRD PARTY WITHOUT  
WRITTEN PERMISSION.

OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

finish:			
(b) SEE TABLE			
1 x c	Ä 3037	13.06.2008	Petker
4 x b	Ä 2518	02.06.06	HS
rev.	description	date	name

tolerance  
DIN ISO 2768-m



2001	date	name
drawn	18.05.	E. Mickenbecker
appd.	18.05.	J. Parei
norm		
d-old		

**CONEC®**

scale: 5:1

material: SEE TABLE (b)

title:  
**JACKSCREW**  
4.40UNCx16.4mm  
FOR ROTATING JACKSCREW SYSTEM

dwg no: AutoCAD 2000

7401A029A

part no: SEE TABLE (b)

DIN-A  
4  
sh: 1/1

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[740-366770](#)