







Technical specification:

Rated voltage: IEC 61076-2-101	5pos 60 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Sealing:	FPM
Coupling nut/ screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:


Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220

Contact assignment:

1) brown	■
2) white	■
3) blue	■
4) black	■
5) green-yellow	■

Part no:	Description:	Length L:	Cable:
43-14677	SAL - 12 - RKW5 - RSW5 - 0,3 / A1 / A1090	0,3m	PVC, grey, 5x0,34mm ² Cable: 781-A13500
43-14678	SAL - 12 - RKW5 - RSW5 - 0,6 / A1 / A1090	0,6m	
43-14679	SAL - 12 - RKW5 - RSW5 - 1,5 / A1 / A1090	1,5m	
43-14680	SAL - 12 - RKW5 - RSW5 - 3,0 / A1 / A1090	3m	
43-xxxxx	SAL - 12 - RKW5 - RSW5 - ... / A1 / A1090	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant		 dim. in mm		title: Connecting cable M12x1, female connector angled - male connector angled	
		date	name		
	tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%	drawn	19.01.11	Franz	dwg no: 43K1A1296
		appd.	19.01.11	Mankopf	
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				part no: see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-14677](#) [43-14678](#) [43-14680](#) [43-14679](#)