







Technical specification:

Rated voltage: IEC 61076-2-101	3pos 250 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Sealing:	FPM
Coupling nut/ screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:


Recommended torque:	0,6 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 13: 36-000220

Contact assignment:

1) brown	■
3) blue	■
4) black	■

Part no:	Description:	Length L:	Cable:
43-14657	SAL - 12 - RKW3 - RSW3 - 0,3 / K1 / A1090	0,3m	TPU, UL 20549, black, 3x0,34mm ² Cable: 781-K13300
43-14658	SAL - 12 - RKW3 - RSW3 - 0,6 / K1 / A1090	0,6m	
43-14659	SAL - 12 - RKW3 - RSW3 - 1,5 / K1 / A1090	1,5m	
43-14660	SAL - 12 - RKW3 - RSW3 - 3,0 / K1 / A1090	3m	
43-xxxxx	SAL - 12 - RKW3 - RSW3 - ... / K1 / A1090	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant		 dim. in mm		title: Connecting cable M12x1, female connector angled - male connector angled	
		date	name		
	tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%	drawn	18.01.11	Franz	dwg no: 43K1A1291
		appd.	18.01.11	Mankopf	
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				part no: see table

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[43-14659](#) [43-14660](#) [43-14658](#) [43-14657](#)