

4

3

2

1

used for:

DIN 41651

B

4

13.9

POS.

B ±0.2

Part-N0.

10

17.30

140X10059X

14

22.40

140X10069X

16

24.90

140X10079X

20

30.00

140X10089X

26

37.60

140X10099X

34

47.80

140X10109X

40

55.40

140X10119X

50

68.10

140X10129X

60

80.80

140X10139X

64

85.85

140X10159X

Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL

CUSTOMER APPROVAL DATE:

NAME:

TITLE:

COMPANY NAME:

APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL

NOTES:

1. INSULATORS: PBT GV, V0, UL 94, GREY RAL 7035

2. OPERATING TEMPERATURE RANGE: -55°C TO +125°C

tolerance



scale:

2:1

material:

SEE NOTES

title:

STRAIN RELIEF

10-64pos.

dwg no:

AutoCAD 2000

DIN-A

14K1A013

4

sh: 1/1

part no:

SEE TABLE

rev.

description

date

name

CONEC®

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[140X10109X](#) [140X10119X](#) [140X10079X](#) [140X10069X](#) [140X10089X](#) [140X10129X](#) [140X10159X](#) [140X10139X](#)
[140X10059X](#)