









NOTES:

1. METAL SHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. HIGH POWER CONTACTS 20A: COPPER ALLOY
PLATING, MATING AREA: GOLD FLASH over NICKEL
PLATING, TERMINATION SIDE: 160-240µm TIN over 80µm NICKEL
4. SIGNAL CONTACTS: COPPER ALLOY;
PLATING: GOLD FLASH over NICKEL
5. METAL BRACKETS: ZINC DIE CAST; 300µm COPPER/40-120µm NICKEL/120-200µm TIN
6. THREADED INSERTS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
7. FIXING-PLATES: PBT GF UL 94 V-0, BLACK
8. P.C.B. HOLE DRILLINGS ON SHEET 2
9. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
10. CONNECTOR IS PART MARKED: 13-001023 CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm		scale: 2:1			
								material: see notes			
				DO NOT ALTER CAD DRAWING BY HAND						title: D-SUB COM. DUAL PORT 19,05mm / Male 7W2P reverse / Male 7W2P with threaded insert, metal bracket, fixing-plate	
				date	name		dwg no: 13K1A4610 part no: 13-001023		DIN-A3 sh: 1/2		
				drawn 13.03.14	Herneboel						
				appd. 17.03.14	Lehmenkühler						
				norm							
				d-old							
											
a	Original										
rev.	description	date	name								

CONEC



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance		 dim. in mm	scale: 4:1			
								material: see sheet 1			
						date	name		title: P.C.B. HOLE DRILLINGS D-SUB Combination Dual Port 19,05mm Male 7W2P reverse /Male 7W2P		
						drawn	13.03.14	Henneboel			
						appd.	17.03.14	Lehmenkühler			
						norm					
						d-old			dwg no:		
								DIN-A3			
										13K1A4610	
	a	Original								sh:2/2	
rev.	description	date	name	part no: SEE SHEET 1							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[13-001023](#)