









NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. HIGH POWER CONTACTS 20A: COPPER ALLOY
PLATING, MATING AREA: GOLD FLASH over NICKEL
PLATING, TERMINATION SIDE: 160-240µin TIN over 80µin NICKEL
4. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
5. METAL BRACKETS: ZINC DIE CAST; 300µin COPPER/40-120µin NICKEL/120-200µin TIN
6. THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
7. FIXING-PLATES: PBT GF UL 94 V-0, BLACK
8. P.C.B. HOLE DRILLINGS ON SHEET 2
9. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
10. CONNECTOR IS PART MARKED: 13-001073 CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH										tolerance		 dim. in mm	scale: 2:1											
													material: see notes											
															date	name		title: D-SUB COM. DUAL PORT 19,05mm / Male 7W2P reverse / Female 7W2S with threaded insert, metal bracket, fixing-plate						
															drawn	01.07.13	Henneboel							
															appd.	01.07.13	Koch							
															norm									
															d-old									
																			dwg no:		DIN-A3			
										a	Original								13K1A4363				sh: 1/2	
										rev.	description	date	name						part no: 13-001073					

CONEC



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance		 dim. in mm	scale: 2:1	
								material: see sheet 1	
						date	name	title: P.C.B. HOLE DRILLINGS D-SUB Combination Dual Port 19,05mm Male 7W2P reverse / Female 7W2S	
					drawn	01.07.13	Henneboel		
					appd.	01.07.13	Koch		
					norm				
					d-old				
							dwg no: 13K1A4363		DIN- A3 sh: 2/2
	a	Original							
	rev.	description	date	name					
DO NOT ALTER CAD DRAWING BY HAND		part no: SEE SHEET 1							

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[13-001073](#)