


Contact assignment:

- 1 brown
- 2 white
- 3 blue
- 4 black

Technical specification:

Rated voltage: IEC 60664-1	300 V
Overvoltage category: IEC 60664-1	2
Overvoltage: IEC 60664-1	2,7 kV
Current rating: IEC 60512-3 at 40°C	0,75mm ² 1,5mm ² 8 A 10 A
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 68, in mated condition
Temperature range:	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100
Termination:	crimped

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU, UL 94
Coupling screw:	CuZn, nickel plated
Moulding body:	TPU, UL 94, grey




Part no:	Description:	Length L:	Cable:
41-01044	SAL - 7/8 - RS4 - 2 / K1	2m	TPU, UL 20549, black, 4x0,75mm ² Cable: 781-K1740G
41-01045	SAL - 7/8 - RS4 - 3 / K1	3m	
41-01046	SAL - 7/8 - RS4 - 5 / K1	5m	
41-01047	SAL - 7/8 - RS4 - 10 / K1	10m	
41-xxxxx	SAL - 7/8 - RS4 - ... / K1	x	
41-01141	SAL - 7/8 - RS4 - 2 / K1 / 150	2m	TPU, UL 20549, black, 4x1,50mm ² Cable: 781-K1840G
41-01142	SAL - 7/8 - RS4 - 3 / K1 / 150	3m	
41-01143	SAL - 7/8 - RS4 - 5 / K1 / 150	5m	
41-01144	SAL - 7/8 - RS4 - 10 / K1 / 150	10m	
41-xxxxx	SAL - 7/8 - RS4 - ... / K1 / 150	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND

Directive 2011/65/EU RoHS compliant

Index: d 24.04.14 MG Ä5178 Cable 781-K18400 superseded by 781-K1840G, data sheet revised, temperature range: IEC removed		 dim. in mm		title: Male connector 7/8" axial	
		date	name		
tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%		drawn	19.10.07	Mankopf	dwg no: 41K1A320
		appd.	19.01.07	Franz	
general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm					part no: see table
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[41-01046](#) [41-01045](#) [41-01047](#) [41-01044](#) [41-01142](#) [41-01143](#) [41-01141](#)