





Technical specification :

Rated voltage: IEC 61076-2-104	60 V
Current rating: IEC 61076-2-104	3 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range:	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100
Materials:	
Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	PA, UL 94
Sealing:	FPM
Coupling nut/ screw:	GD-Zn, nickel plated
Moulding body:	TPU, UL 94, grey

Installation specification:


Recommended torque:	0,4 Nm at width across flats 9
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 9: 36-000210

Contact assignment 4pos:



Part no:	Description:	Length L:	Cable:
42-11788	SAL - 8 - DS4 - 2RK4 - 0,3 / 0,3 / A1	0,3m	PVC, grey, 4x0,25mm ² Cable: 781-A12400
42-11789	SAL - 8 - DS4 - 2RK4 - 0,6 / 0,6 / A1	0,6m	
42-11790	SAL - 8 - DS4 - 2RK4 - 1,5 / 1,5 / A1	1,5m	
42-11791	SAL - 8 - DS4 - 2RK4 - 3 / 3 / A1	3,0m	
42-xxxxx	SAL - 8 - DS4 - 2RK4 - ... / ... / A1	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant			 dim. in mm		title: Duo-distributor, male connector M8x1 axial - 2x female connector M8x1 axial
			date	name	
	tolerance of cable: L <= 4m: L + 40mm L > 4m: L + 1%		drawn	25.10.12	Fromm
			appd.	25.10.12	Mankopf
	general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm				dwg no: 42K1A420
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				part no: see table



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

[42-11790](#) [42-11791](#) [42-11788](#) [42-11789](#)