




NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACTS ON POS. A1 - A5
5. CONNECTOR IS PART MARKED: 3017W5PAM99A10X CONEC ABC

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH										tolerance				 dim. in mm		scale: 2:1 (5:1)							
																material: SEE NOTES							
															date	name		title: D-SUB COMBINATION MALE 17W5P SOLDER CUP					
															drawn	04.01.2016 Unkrüer							
															appd.	04.01.2016 Lehmenkühler							
															norm								
															d-old			dwg no:				DIN-A3 sh: 1	
																							
										a	Original						13K1A5132						
										rev.	description		date	name		part no: 3017W5PAM99A10X							

RoHS compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[3017W5PAM99A10X](#)