







NOTES:

1. METALSHELLS: COPPER ALLOY; min. 315µm TIN over 40-80µm NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK (b)
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL (b)
SOLDER CUP ACCEPTS CABLE AWG 22
4. CONNECTOR IS PART MARKED: 4HDD44SAM99A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH					tolerance		 dim. in mm	scale: 2:1 (5:1)			
								material: SEE NOTES			
					date	name	title: D-SUB HD FEMALE 44pos. SOLDER CUP for installation into water resistant hood				
					drawn	20.04.10 Henneboel					
					appd.	20.04.10 Fischer					
					norm						
					d-old		dwg no: Inventor 10 15K3A338 part no: 4HDD44SAM99A10X				
	2 x b	Ä3897	03.01.11	K.H.						DIN-A3 sh: 1	
	a	Origin									
	rev.	description	date	name							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

4HDD44SAM99A10X