




Notes:

1. Electrical:

- Meets EIA/TIA-568-B.2-10 Cat. 6A Channel Specification
- Connector Operating Temperature: -40°C to +85°C

2. Materials and Finish:

- Coupling Ring: Brass, Nickel Plated
- ⑥ - Plug Housing: Zinc Die-Cast, Nickel Plated
- Interfacial Seal: Silicon, Color: White
- Cable Gland: Brass, Nickel Plated
- Cable Gland Seal: NBR, Color: Black
- Cat.6A RJ45 Plug Metal Shell: Copper Alloy, Nickel Plated
- Cat.6A RJ45 Plug Plastic Housing: Clear Polycarbonate UL94 V-2
- Cat.6A RJ45 Plug Contacts: Phosphor Bronze, Finish: 50 u" Gold min. over Nickel
- Cable: Cat.6A SFTP, 4 Pairs, AWG26, Stranded, Jacket Color: Black

RoHS Compliant

©

Patch Cord Length L	Part Number
1m ± 0.02m	17-180504
2m ± 0.03m	17-150724
3m ± 0.03m	17-180514
4m ± 0.04m	17-150734
5m ± 0.05m	17-150744
10m ± 0.10m	17-180524
20m ± 0.20m	17-180534

*Note: Special cable length and blue cable up to 20m are available please contact factory
Cable length > 20m cannot guarantee to meet TIA/EIA-568-C.2 Cat. 6A Specification.

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF CONEC CORPORATION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3°		Autodesk Inventor	Scale: NTS	Dim. in meter	
	Name	Title	Approval Date	2011	Date		Name	Material: See Notes	
				Draw.	Sept. 28		Vincent Ke	Cat. 6A RJ45 Ethernet Patch Cords IP67 Industrial to IP67 Industrial M28 Thread Metal Version	
				Appd.	Sept. 28		J. Chaudry	Drawing No.: 17K1A278	
				Norm				Part No.: SEE PART NUMBER TABLE	
	c	1 x c	Apr./15/2015	Vincent Ke	D-old			DIN A3	
	b	1 x b	Jun/23/2014	Vincent Ke				Sheet 1/1	
	a	original							
	Rev.	Changes	Date	Name					

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[17-150724](#)